



■ Series 4727 • VariMill

Material Group		 										Recommended feed per tooth (fz = mm/th) for side milling (A).			
		Side Milling (A)													
		Finishing					Roughing					D1 – Diameter			
		A		TiAlN			A		TiAlN						
		ap	ae	Cutting Speed – vc m/min			ap	ae	Cutting Speed – vc m/min			mm	12,0	16,0	20,0
P	1	Ap1 max	0,05 x D*	300	–	400	Ap1 max	0,2 x D	150	–	200	fz	0,083	0,101	0,114
	2	Ap1 max	0,05 x D*	280	–	380	Ap1 max	0,2 x D	140	–	190	fz	0,083	0,101	0,114
	3	Ap1 max	0,05 x D*	240	–	320	Ap1 max	0,2 x D	120	–	160	fz	0,070	0,087	0,101
	4	Ap1 max	0,05 x D*	180	–	300	Ap1 max	0,2 x D	90	–	150	fz	0,062	0,077	0,088
	5	Ap1 max	0,05 x D*	120	–	200	Ap1 max	0,2 x D	60	–	100	fz	0,056	0,070	0,081
	6	Ap1 max	0,05 x D*	100	–	150	Ap1 max	0,2 x D	50	–	75	fz	0,047	0,057	0,065
M	1	Ap1 max	0,05 x D*	180	–	230	Ap1 max	0,2 x D	90	–	115	fz	0,070	0,087	0,101
	2	Ap1 max	0,05 x D*	120	–	160	Ap1 max	0,2 x D	60	–	80	fz	0,056	0,070	0,081
	3	Ap1 max	0,05 x D*	120	–	140	Ap1 max	0,2 x D	60	–	70	fz	0,047	0,057	0,065
K	1	Ap1 max	0,05 x D*	240	–	300	Ap1 max	0,2 x D	120	–	150	fz	0,083	0,101	0,114
	2	Ap1 max	0,05 x D*	220	–	260	Ap1 max	0,2 x D	110	–	130	fz	0,070	0,087	0,101
	3	Ap1 max	0,05 x D*	200	–	260	Ap1 max	0,2 x D	100	–	130	fz	0,056	0,070	0,081
S	1	Ap1 max	0,05 x D*	100	–	180	Ap1 max	0,2 x D	50	–	90	fz	0,070	0,087	0,101
	2	Ap1 max	0,05 x D*	50	–	80	Ap1 max	0,2 x D	25	–	40	fz	0,070	0,087	0,101
	3	Ap1 max	0,05 x D*	120	–	160	Ap1 max	0,2 x D	60	–	80	fz	0,037	0,046	0,054
	4	Ap1 max	0,05 x D*	100	–	120	Ap1 max	0,2 x D	50	–	60	fz	0,052	0,064	0,074
H	1	Ap1 max	0,05 x D*	160	–	280	Ap1 max	0,2 x D	80	–	140	fz	0,062	0,077	0,088

\*For cutting data above, use ae ≤ 0,8mm.

NOTE: Lower value of cutting speed is used for high stock removal applications or for higher hardness (machinability) within group.

Higher value of cutting speed is used for finishing applications or for lower hardness (machinability) within group.

Above parameters are based on ideal conditions. For smaller taper machining centres, please adjust parameters accordingly on >12mm diameters.

For finishing, increase feed per tooth by 20%.

High-Performance Solid Carbide End Mills